
CHARLES RIVER APPAREL FIT GUIDE



MEASUREMENT GUIDE

CHEST/BUST: Tape measure should be placed under arms. Measure at the fullest circumference around your chest.

WAIST: Measure your natural waistline around the narrowest circumference of your waist.

HIPS: Measure at the fullest circumference around your hips.

SLEEVE LENGTH: With elbow bent slightly, measure from center back of your neck, over the shoulder, over to the slightly bent elbow and down to the outer wrist.

INSEAM: Stand and measure the line where the two parts of a pair of pants are sewn together (top of the inside of the leg) to the bottom of your ankle bone.

These sizes and body measurements are intended as a guide to assist with sizing – these are not exact garment measurements. Locate your measurements below, and the chart will tell you the approximate Charles River Apparel size you should fit into. Style specific measurements can be found on our product spec sheets, which are available to download on every product detail page on our website.


| MEN'S SIZE | | | | | | | | | |
|---------------|-------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|
| | XS | S | М | L | XL | 2XL | 3XL | 4XL | 5XL |
| CHEST | 33 - 34 | 35 - 37 | 38 - 40 | 42 - 44 | 46 - 48 | 50 - 52 | 54 - 56 | 58 - 60 | 62 - 64 |
| WAIST | 27 - 28 | 29 - 31 | 32 - 34 | 36 - 38 | 40 - 42 | 44 - 46 | 48 - 50 | 52 - 54 | 56 - 58 |
| SLEEVE LENGTH | 30.5 - 31.5 | 32 - 32.5 | 33 - 33.5 | 34 - 34.5 | 34.5 - 35 | 35 - 35.5 | 36 - 36.5 | 36.5 - 37 | 37.5 - 38 |
| inseam length | 30 | 30.5 | 31 | 31.5 | 32 | 32 | 32 | 32 | 32 |

*For tall sizes: add 1" to the above sleeve length measurement and add 2" to the above inseam length measurement

| WOMEN'S SIZE | | | | | | | |
|---------------|-------------|-------------|-----------|-----------|-----------|---------|---------|
| | XS | S | М | L | XL | 2XL | 3XL |
| SIZE | 2/4 | 6/8 | 10/12 | 14/16 | 18/20 | 22/24 | 26/28 |
| CHEST | 32 - 33 | 34 - 35 | 36 - 38 | 39 - 41 | 42 - 44 | 46 - 48 | 50 - 52 |
| WAIST | 24 - 25 | 26 - 27 | 28 - 30 | 31 - 33 | 34 - 36 | 38 - 40 | 42 - 44 |
| HIP | 34.5 - 35.5 | 36.5 - 37.5 | 38.5 - 40 | 41.5 - 43 | 45 - 47 | 48 - 50 | 52 - 54 |
| SLEEVE LENGTH | 30 - 30.5 | 30.5 - 31 | 31.5 - 32 | 32 - 32.5 | 32.5 - 33 | 33.25 | 33.5 |
| INSEAM LENGTH | 30.5 | 30.5 | 30.5 | 30.5 | 30.5 | 30.5 | 30.5 |

| YOUTH SIZE | | | | | |
|---------------|---------|---------|---------|---------|---------|
| | XS | S | M | L | XL |
| SIZE | 5/6 | 7/8 | 10/12 | 14/16 | 18/20 |
| CHEST | 25 - 26 | 26 - 28 | 28 - 30 | 31 - 33 | 34 - 36 |
| WAIST | 22 - 23 | 23 - 24 | 25 - 26 | 27 - 28 | 29 - 30 |
| SLEEVE LENGTH | 21 - 22 | 23 - 24 | 25 - 27 | 28 - 30 | 31 - 32 |
| inseam length | 21 | 23 | 25 | 27.5 | 30 |

| NECK GAITER | | | | | |
|-----------------------------|----------|--|--|--|--|
| | ONE SIZE | | | | |
| (A) 1/2 OF CIRCUMFERENCE | 9.5″ | | | | |
| (B) HEIGHT | 16.5" | | | | |



| | DOGGIE RAIN JACKET SIZE | | | | | | |
|--|-------------------------|---------|---------|---------|---------|---------|--|
| | | XS | S | М | L | XL | |
| | (A) NECK | 8″-10″ | 10″-12″ | 12″-14″ | 14″-16″ | 16″-18″ | |
| | (B) CHEST | 10″-14″ | 14"-18" | 18″-22″ | 22″-26″ | 26″-30″ | |
| | (C) LENGTH | 6″-8″ | 8″-12″ | 12″-16″ | 16″-20″ | 20"-24" | |



| VIROMASK SHIELD WITH HEIQ" V-BLOCK TECHNOLOGY | | | | | |
|--|----------|--|--|--|--|
| | ONE SIZE | | | | |
| (A) FRONT HEIGHT | 6.75" | | | | |
| (B) BACK HEIGHT | 2.75" | | | | |
| (C) OVERALL WIDTH | 9.25" | | | | |

